

H+M 380 - LED module



Complete LED module for easy and efficient refurbishment of existing **H+M Ø380** variants for surface mount or recessed.

LED and driver spec:

LED type: 324 mm board, 17, 23, or 33 W
 Operational life: min 50,000 hours at ta 25°C, L80B10
 Colour temperature: 2700, 3000, or 4000 Kelvin
 alternatively 2700-6500 K dynamic
 Energy eff. class: 2700 K: E - 3000, 4000, 6500 K: D
 Colour rendering: min 90 Ra
 Colour accuracy: 3 steps SDCM
 Driver: 350-1050 mA driver, dimming optional
 Operational life: min 50,000 hours

Exchange of lamp module:

Recessed fixtures:

Demounting:
 Old fixtures (3 cm visible height): Pull off the outer ring downwards.
 Revised fixtures (2 cm visible height): Turn collar and shade off as one unit anti-clockwise.
 Unfasten the old lamp by demounting cables and plate (2 screws).
 Fasten the new LED module by the existing screws, connect the cables and clips on the LED board.
 Remount/Turn the bottom part clockwise into locked position again.

Surface-mounted fixtures:

The shade is unfixated and can be removed by tipping it upwards in one side.
 Unfasten the old lamp by demounting cables and plate (2 screws).
 Fasten the new LED module by the existing screws, connect the cables and clips on the LED board.
 Replace the shade.

We include a blank label in the consignment. Write the old item number on the label and attach it inside the luminaire.

Variants:

LED module for H+M Ø380 mm, surface mount or recessed									
Item No.	Lamp type		Select colour temperature and other options in the table below.						
1903-	H+M 380, 17 W, 500 mA								
1904-	H+M 380, 23 W, 700 mA								
1968-	H+M 380, 33 W, 1050 mA, Dali								
Combine with:	Colour temperature		Dimming						
	927	2700 K, 90 Ra	V	1-10 V					
	930	3000 K, 90 Ra	D	Dali					
	940	4000 K, 90 Ra							
	9WD	TW, Dali, 90 Ra							
Example:	1904-930D = 23 W LED module, 3000 K, 90 Ra, Dali								
The above LED modules fit the following variants (X stands for colour code):									
	2071, 2171, 256X, 266X								
	2007X, 2107X, 2207X, 2307X, 2807X, 2116X, 2216X, 2217X, 2316X, 2816X								
	2866, 2867, 2868, 2876, 2877, 2878								
	Please take contact if your item number is not in the list.								